



TECHNICAP

216, Chemin du Braousch - 06320 La Turbie / France

Tél : 33 (0)4 92 10 85 68 - Fax : 33 (0)4 92 10 82 98

Email : [technicap@wanadoo.fr](mailto:technicap@wanadoo.fr) / [www.technicap.com](http://www.technicap.com)

<b>MODEL</b>	<b>PPS 3/3</b>
Collecting area (sqm)	0,125
Shape	Cylindro-conical
Baffle material	Phenolic Composite
Baffle Cell diameter	9,5mm
Aspect ratio of a cell	5,26
Number of Samples	12
Volume of Sampling Bottles	250ml
Sampling Interval	Minimum 1 minute
Max. continuous deployment	18 months (24 months with Lithium batteries)
Opérating Temperature	-2° to 37°
Maximum Operating Deph	1000m (PETP) or 5000m (Aluminium) or 6000m (Titanium)
<b>MATERIALS</b>	
Trap body	Glass reinforced polyester (GRP) on an alimentary gel-coat
Carrousel	PETP (very hard thermoplastic)
Sampling Bottles	Polypropylen
Electronics / Motor pressure case	Thermoplastic (PETP/PEEK) or Aluminium alloy anodizing or Titanium
Rotating Mooring Bar	Titanium
Power Supply	12 volt AA alkaline batteries pack (or 12 volt lithium on request)
Drive motor torque	60kg/cm
Time to shift a bottle	7 seconds
Communications	Electronic card and firmware with integrated inclinometer and temperature sensors
<b>DIMENSIONS</b>	
Height	1900
Diameter Max	600
<b>WEIGHT</b>	
In Air	40
In Water	17
<b>DELIVERY : WOOD BOX</b>	
External Dimensions	2000 x 560 x 750
Total Weight	82