



TECHNICAP

216, Chemin du Braousch - 06320 La Turbie / France

Tél : 33 (0)4 92 10 85 68 - Fax : 33 (0)4 92 10 82 98

Email : technicap@wanadoo.fr / www.technicap.com

MODEL	PPS 6/2
Collecting area (sqm)	0,50
Shape	Conical (36°)
Baffle material	Phenolic Composite
Baffle Cell diameter	9,5mm
Aspect ratio of a cell	5,26
Number of Samples	12 or 24
Volume of Sampling Bottles	250ml or 500ml
Sampling Interval	Minimum 1 minute
Max. continuous deployment	18 months (24 months with Lithium batteries)
Opérating Temperature	-2° to 37°
Maximum Operating Deph	1000m (PETP) or 5000m (Aluminium) or 6000m (Titanium)
MATERIALS	
Trap body	Glass reinforced polyester (GRP) on an alimentary gel-coat
Carrousel	PETP (very hard thermoplastic)
Sampling Bottles	Polypropylen
Electronics / Motor pressure case	Thermoplastic (PETP/PEEK) or Aluminium alloy anodizing or Titanium
Rotating Mooring Bar	Titanium
Power Supply	12 volt AA alkaline batteries pack (or 12 volt lithium on request)
Drive motor torque	60kg/cm
Time to shift a bottle	7 seconds
Communications	Electronic card and firmware with integrated inclinometer and temperature sensors
DIMENSIONS	
Height	1820
Diameter Max	1020 x 1020
WEIGHT	
In Air	90
In Water	37
DELIVERY : WOOD BOX	
External Dimensions	1970 x 1150 x 1230
Total Weight	207